


Eaton TP637

Catalog Number: TP637

Eaton Crouse-Hinds series Gang Box, (6) 1/2" and 3/4" concentric, VS, Conduit (no clamps), 2-1/2", (2) 1/2" and 3/4" concentric, Steel, Three-gang, (3) 1/2" and 3/4" concentric, Non-gangable, 46.5 cubic inch capacity



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series gang box	TP637
UPC	Product Length/Depth
786189106374	5.56 in
Product Height	Product Width
2.5 in	3.75 in
Product Weight	
1.43 lb	

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Product specifications

Depth

2-1/2"

Type

Non-gangable

Number of gangs

Three-gang

Capacity

46.5 cubic in

Conduit/cable

Conduit (no clamps)

Bracket style

VS

End Knockouts

(2) 1/2 in and 3/4 in concentric

Side knockouts

(3) 1/2 in and 3/4 in concentric

Bottom Knockouts

(6) 1/2 in and 3/4 in concentric

Material

Steel

Resources

Catalogs

[Crouse-Hinds series Steel Switch Boxes catalog page](#)

Certification reports

[Steel Switch Boxes UL certification](#)

[Steel Switch Boxes Canadian certification](#)

Specifications and datasheets

[Eaton Specification Sheet - TP637](#)

[Steel Outlet Boxes for Electrical Systems](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)