

Eaton TR1307V-BOX

Catalog Number: TR1307V-BOX

Eaton residential grade decorator duplex receptacle, #14-10 AWG, 20A, Commercial|Residential, Flush, 125V, Side wire, Violet, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Duplex, Screw, Thermoplastic, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton residential grade decorator duplex receptacle	TR1307V-BOX
	UPC
	032664729676
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.74 in	0.154 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Decorator duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Thermoplastic

Packaging type

ED Box

Color

Ivory

Violet

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR1307V-BOX](#)

[Duplex tamper resistant receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face

PVC body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)