

Eaton TR1307W-BOX

Catalog Number: TR1307W-BOX

Eaton residential grade decorator duplex receptacle, #14-10 AWG, 20A, Commercial|Residential, Flush, 125V, Side wire, White, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Duplex, Screw, Thermoplastic, ED Box



Photo is representative

General specifications

| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton residential grade decorator duplex receptacle | TR1307W-BOX |
| | UPC |
| | 032664729683 |
| Product Length/Depth | Product Height |
| 1.31 in | 4.19 in |
| Product Width | Product Weight |
| 0.74 in | 0.154 lb |
| Certifications | |
| cULus Listed | |
| NOM | |

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Decorator duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Side wire

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Thermoplastic

Packaging type

ED Box

Color

White

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR1307W-BOX](#)

[Duplex tamper resistant receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face

PVC body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)