

Eaton TR1877A-BXSP

Catalog Number: TR1877A-BXSP

Eaton commercial specification grade single receptacle, #14-10 AWG, 20A, Flush, 125V, Side, Almond, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, Two-pole, Three-wire, Single, Screw, PVC



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade single receptacle	TR1877A-BXSP
	UPC
	032664668340
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.87 in	0.155 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Special features

Tamper resistant, auto-grounding, enhanced ground contacts

Amperage Rating

20A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

Auto-grounding

Enhanced ground contacts

Application

Commercial

Device grade

Commercial

Wiring method

Side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

PVC

Color

Almond

Connection type

Screw

Allowable wire size

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR1877A-BXSP](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant thermoplastic face

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)