

Eaton TR270W

Catalog Number: TR270W

Eaton residential grade duplex receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Side and push, White, Brass, Impact-resistant thermoplastic face, PVC body, 5-15R, Duplex, Screw, Thermoplastic, Core pack



General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	TR270W
	UPC
	032664666537
Product Length/Depth	Product Height
1.24 in	4 in
Product Width	Product Weight
0.79 in	0.01 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel	Resources
Device type	Multimedia
Receptacle	Residential straight blade receptacles
Type	Specifications and datasheets
Duplex receptacle	Eaton Specification Sheet - TR270W
Amperage Rating	Duplex tamper resistant receptacles spec sheet
15A	
Voltage rating	
125V	
Contact material	
Brass	
Features	
Tamper resistant	
Application	
Commercial/residential	
Device grade	
Standard grade	
Wiring method	
Side and push	
Number of wires	
3	
Mounting method	
Flush	
Number Of Poles	
Two-pole	
Style type	
Standard	
Material	
Thermoplastic	
Packaging type	
Core pack	
Color	
White	
Connection type	
Screw	

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant thermoplastic face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia