

Eaton TR270W-10-L

Catalog Number: TR270W-10-L

Eaton residential grade duplex receptacle, Tamper resistant, 10-pckg, , #14-10 AWG, 15A, Flush, 125V, White, Brass, Impact-resistant thermoplastic face,PVC body, 5-15R, Two-pole, Three-wire, Screw,

General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	TR270W-10-L
	UPC
	032664749957
Product Length/Depth	Product Height
1.24 in	4 in
Product Width	Product Weight
0.79 in	1.06 lb
Certifications	
NOM	
cULus Listed	



defaultTaxonomyAttributeLabel

Device type

Receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

10-pack

Application

Residential

Device grade

Standard grade

Wiring method

Side and push

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Color

White

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR270W-10-L](#)

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face

PVC Body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)