

# Eaton TR5262CDGN

Catalog Number: TR5262CDGN

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle,#14-10 AWG,15A,Flush,125V,Back and side,Green,Brass,Impact-resistant thermoplastic face,PVC body,5-15R,Screw,Core pack,Tamper-resistant|Auto-grounding|Dual



## General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	TR5262CDGN
	UPC
	032664760655
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.84 in	0.222 lb
Certifications	
cULus Listed	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Dual controlled

Tamper resistant

Dual-controlled

### Application

Industrial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Thermoplastic

### Packaging type

Core pack

### Color

Green

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR5262CDGN](#)

[Arrow Hart heavy-duty controlled receptacles](#)

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face

PVC body

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)