

Eaton TR5362CDBK

Catalog Number: TR5362CDBK

Eaton Arrow Hart heavy duty industrial specification grade duplex receptacle, Tamper resistant, auto-grounding, Dual control, #14-10 AWG, 20A, Flush, 125V, Black, Brass, Impact-resistant thermoplastic face, PVC body, 5-20R, 2-pole, 3-wire, ,



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	TR5362CDBK
	UPC
	032664744617
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.84 in	0.22 lb
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Dual control

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Auto-grounding

Dual-controlled

Application

Industrial

Device grade

Construction

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Color

Black

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

Resources

Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR5362CDBK](#)

5-20R

Design type

Straight blade

Face/body material

PVC Body

Impact-resistant thermoplastic face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)