

# Eaton TR5362W

Catalog Number: TR5362W

Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle,#14-10 AWG,20A,Industrial,Flush,125V,Back and side,White,Brass,Impact-resistant thermoplastic face,PVC body,5-20R,Duplex,Screw,Thermoplastic,Core pack

## General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty industrial specification grade duplex receptacle	TR5362W
	UPC
	032664718632
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.84 in	0.22 lb
Certifications	
cULus Listed	



## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Tamper resistant

### Application

Industrial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Thermoplastic

### Packaging type

Core pack

### Color

White

### Connection type

Screw

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR5362W](#)

[Arrow Hart heavy-duty straight blade duplex receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant thermoplastic face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)