

# Eaton TR5797

Catalog Number: TR5797

Eaton commercial specification grade single receptacle,#14-10 AWG,15A,Commercial,Floor,Recessed,125V,Back and side,Brass,Brass,Impact-resistant thermoplastic face and back body,Brass floor box,5-15R,Single,Screw,Thermoplastic,Core pack



## General specifications

Product Name	Catalog Number
Eaton floor box with tr receptacles	TR5797
UPC	Product Length/Depth
032664726040	2.75 in
Product Height	Product Width
4.5 in	3.5 in
Product Weight	Certifications
0.5 lb	cULus Listed

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Special features

Tamper-resistant  
Floor box assembly

### Type

Floor box assembly

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Tamper-resistant  
Floor box assembly

### Application

Commercial

### Device grade

Specialty standard

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Recessed  
Floor

### Number Of Poles

Two-pole

### Style type

Floor box, Heavy duty

### Material

Thermoplastic

### Packaging type

Core pack

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - TR5797](#)

[Recessed and floor box receptacles spec sheet](#)

Color

Brass

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Brass floor box

Receptacle type

Single



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)