

Eaton TR6250W-BOX

Catalog Number: TR6250W-BOX

Eaton heavy-duty industrial specification grade decorator single receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Back and side, White, Brass, Impact-resistant thermoplastic face and back body, 5-15R, Single, Screw, PVC, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton heavy-duty industrial specification grade decorator single receptacle	TR6250W-BOX
	UPC
	032664665394
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.84 in	0.132 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Decorator single receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Application

Commercial

Device grade

Heavy-duty industrial specification grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

PVC

Packaging type

ED Box

Color

White

Connection type

Screw

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR6250W-BOX](#)

[Arrow Hart heavy-duty straight blade decorator receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Receptacle type

Single



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)