

# Eaton TR6252W-BOX

Catalog Number: TR6252W-BOX

Eaton heavy-duty industrial specification grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Back and side, White, Brass, Impact-resistant thermoplastic face and back body, 5-15R, Duplex, Screw, PVC, ED Box



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy-duty industrial specification grade decorator duplex receptacle	TR6252W-BOX
	<b>UPC</b>
	032664668463
<b>Product Length/Depth</b>	<b>Product Height</b>
1.32 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.84 in	0.21 lb
<b>Certifications</b>	
cULus Listed	
NOM	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Auto-grounding

Tamper resistant

### Application

Commercial

### Device grade

Heavy-duty industrial specification grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Material

PVC

### Packaging type

ED Box

### Color

White

### Connection type

Screw

## Resources

### Brochures

[Spec grade receptacles brochure](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR6252W-BOX](#)

[Arrow Hart heavy-duty straight blade decorator receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)