

# Eaton TR6352CDB

Catalog Number: TR6352CDB

Eaton commercial specification grade decorator duplex receptacle, Tamper resistant, Dual control, #14-10 AWG, 20A, Flush, 125V, Brown, Brass, Impact-resistant thermoplastic face and back body, 5-20R, Two-pole, Three-wire, Screw,



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton heavy-duty industrial specification grade decorator duplex receptacle	TR6352CDB
	<b>UPC</b>
	032664745072
<b>Product Length/Depth</b>	<b>Product Height</b>
1.32 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.84 in	0.22 lb
<b>Certifications</b>	
cULus Listed	
NOM	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Dual control

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Tamper resistant

Auto-grounding

Dual-controlled

### Application

Commercial

### Device grade

Commercial specification grade

### Wiring method

Back and side

### Number of wires

Three-wire

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Decorator

### Color

Brown

### Connection type

Screw

### Allowable wire size

#14-10 AWG

### NEMA configuration

## Resources

### Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TR6352CDB](#)

5-20R

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)