

Eaton TR6352CHLA

Catalog Number: TR6352CHLA

Eaton commercial specification grade decorator duplex receptacle, Tamper resistant, Half control, #14-10 AWG, 20A, Flush, 125V, Light almond, Brass, Impact-resistant thermoplastic face and back body, 5-20R, Two-pole, Three-wire, Screw,



General specifications

Product Name	Catalog Number
Eaton heavy-duty industrial specification grade decorator duplex receptacle	TR6352CHLA
	UPC
	032664745171
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.84 in	0.22 lb
Certifications	
NOM	
cULus Listed	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Half control

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Auto-grounding

Half controlled

Application

Commercial

Device grade

Commercial specification grade

Wiring method

Back and side

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Color

Light almond

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

Resources

Brochures

[Spec grade receptacles brochure](#)

[Controlled receptacles sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR6352CHLA](#)

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)