

Eaton TR780W-BOX

Catalog Number: TR780W-BOX

Eaton commercial specification grade decorator duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Push and side, White, Brass, Impact-resistant thermoplastic face and back body, 5-15R, Duplex, Screw, Thermoplastic, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade decorator duplex receptacle	TR780W-BOX
	UPC
	032664750120
Product Length/Depth	Product Height
2.72 in	4.48 in
Product Width	Product Weight
2 in	0.211 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Recessed

Tamper resistant

Application

Commercial

Device grade

Specialty standard

Wiring method

Push and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Recessed

Material

Thermoplastic

Packaging type

ED Box

Color

White

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR780W-BOX](#)

[Recessed and floor box receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic face and back body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)