

Eaton TR8255LA

Catalog Number: TR8255LA

Eaton combination USB charger with duplex receptacle, Tamper resistant, 15A, Flush mount, 125 Vac, 5 Vdc, Wire leads, Light almond, Brass, 5-15R, Two-pole, three-wire, grounding, Decorator, Thermoplastic



General specifications

Product Name	Catalog Number
Eaton hospital grade combination USB charger with duplex receptacle	TR8255LA
	UPC
	032664741623
Product Length/Depth	Product Height
1.74 in	4.454 in
Product Width	Product Weight
1.955 in	1 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Type

Type A

Amperage Rating

15A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

3.1A Charging

Wire leads

Wiring method

Wire leads

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Color

Light almond

Material

Thermoplastic

Style

Decorator

NEMA configuration

5-15R

Combination type

USB

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[USB charging devices brochure](#)

Multimedia

[Eaton USB Charging Receptacles](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

[Eaton's USB charging receptacles - Never miss a moment](#)

[Introduction to USB-C Duplex Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR8255LA](#)

[Arrow Hart USB charger with hospital grade tamper resistant duplex receptacle spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)