

Eaton TR8362BK

Catalog Number: TR8362BK

Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, Black, Brass, Impact-resistant nylon face, PVC body, 5-20R, Duplex, Screw, Glass-filled nylon, Core pack



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle	TR8362BK
	UPC
	032664746123
Product Length/Depth	Product Height
1.32 in	4.19 in
Product Width	Product Weight
0.88 in	0.247 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Terminal guards

Tamper resistant

Auto-grounding

Application

Healthcare

Device grade

Extra heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Glass-filled nylon

Packaging type

Core pack

Color

Black

Connection type

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TR8362BK](#)

[Extra heavy-duty hospital grade tamper resistant duplex receptacles spec sheet](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Design type

Straight blade

Face/body material

Impact-resistant nylon face

PVC body

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)