

Eaton TRAFCI15A

Catalog Number: TRAFCI15A

Eaton AFCI receptacle, Visual trip indicator light, 15A, 125V, Back wire and side wire, AFCI, Almond, Brass, Receptacle, Tamper resistant, PVC, 5-15R, Two-pole, three-wire, grounding



General specifications

Product Name	Catalog Number
Eaton AFCI receptacle	TRAFCI15A
UPC	Product Length/Depth
032664739408	2 in
Product Height	Product Width
4.625 in	4.813 in
Product Weight	Certifications
0.001 lb	cULus Listed

defaultTaxonomyAttributeLabel

Device type

Receptacle

Amperage Rating

15A

Voltage rating

125V

Circuit interrupter type

AFCI

Contact material

Brass

Features

Tamper resistant

Application

Residential
Commercial

Wiring method

Back and side wire

Allowable wire size

#14 - 10 AWG

NEMA configuration

5-15R

Torque rating

16 lbf-inch

Environmental conditions

Tamper resistant

Mounting method

Flush

Color

Almond

Face/body material

PVC
Polycarbonate

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[AFCI receptacle brochure](#)

Installation instructions

[AFCI instruction sheet](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - TRAFCI15A](#)

[AFCI receptacle spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)