

Eaton TRAFCI15A-BOX

Catalog Number: TRAFCI15A-BOX

Eaton AFCI receptacle, Visual trip indicator light, box, 15A, 125V, Back wire and side wire, AFCI, Almond, Brass, Receptacle, Tamper resistant, PVC, 5-15R, Two-pole, three-wire, grounding

General specifications



Photo is representative

Product Name

Eaton AFCI receptacle

Catalog Number

TRAFCI15A-BOX

UPC

032664741791

Product Length/Depth

2 in

Product Height

5.1 in

Product Width

3.25 in

Product Weight

0.001 lb

Warranty

2 year limited

Certifications

cULus Listed

defaultTaxonomyAttributeLabel

Device type

Receptacle

Amperage Rating

15A

Voltage rating

125V

Circuit interrupter type

AFCI

Contact material

Brass

Features

Tamper resistant

Application

Residential

Commercial

Wiring method

Back and side wire

Allowable wire size

#14 - 10 AWG

NEMA configuration

5-15R

Torque rating

16 lbf-inch

Environmental conditions

Tamper resistant

Mounting method

Flush

Color

Almond

Face/body material

PVC

Polycarbonate

Receptacle type

Two-pole, three-wire, grounding

Resources

Brochures

[AFCI receptacle brochure](#)

Installation instructions

[AFCI instruction sheet](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - TRAFCI15A-BOX](#)

[AFCI receptacle spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)