

# Eaton TRAFCI20BK

Catalog Number: TRAFCI20BK

Eaton AFCI receptacle, Tamper resistant, #14 - 10 AWG, 20A, Residential, Commercial, Flush, 125 V, AFCI, Back and side wire, Black, Brass, Receptacle, Tamper resistant, Polycarbonate, 5-20R, Two-pole, three-wire, grounding



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton AFCI receptacle	TRAFCI20BK
<b>UPC</b>	<b>Product Length/Depth</b>
032664739491	2 in
<b>Product Height</b>	<b>Product Width</b>
4.625 in	4.813 in
<b>Product Weight</b>	<b>Warranty</b>
0.37 lb	2 year limited
	Refer to warranty document.
<b>Certifications</b>	
cULus Listed	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Circuit interrupter type

AFCI

### Contact material

Brass

### Features

Tamper resistant

### Application

Residential  
Commercial

### Wiring method

Back and side wire

### Allowable wire size

#14 - 10 AWG

### NEMA configuration

5-20R

### Torque rating

16 lbf-inch

### Environmental conditions

Tamper resistant

### Mounting method

Flush

### Color

Black

### Face/body material

PVC  
Polycarbonate

### Receptacle type

Two-pole, three-wire, grounding

## Resources

### Brochures

[AFCI receptacle brochure](#)

### Installation instructions

[AFCI instruction sheet](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - TRAFCI20BK](#)

[AFCI receptacle spec sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)