

# Eaton TRAFGF15BK

Catalog Number: TRAFGF15BK

Eaton AFGF receptacle, Tamper resistant, Self-test, #14 - 10 AWG, 15A, Residential, Commercial, Flush, 125 V, AFGF, Back and side wire, Black, Brass, Receptacle, Tamper resistant, Polycarbonate, 5-15R, Two-pole, three-wire, grounding



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton AFGF receptacle	TRAFGF15BK
<b>UPC</b>	<b>Product Length/Depth</b>
032664747564	2.815 in
<b>Product Height</b>	<b>Product Width</b>
4.625 in	2.01 in
<b>Product Weight</b>	<b>Certifications</b>
0.401 lb	cULus Listed
	CSA Certified
	UL Listed
	NOM

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Self-test

### Amperage Rating

15A

### Voltage rating

125V

### Circuit interrupter type

AFGF

### Contact material

Brass

### Features

Tamper resistant

### Application

Residential

Commercial

### Wiring method

Back and side wire

### Allowable wire size

#14 - 10 AWG

### NEMA configuration

5-15R

### Torque rating

16 lbf-inch

### Environmental conditions

Tamper resistant

### Mounting method

Flush

### Color

Black

### Face/body material

PVC

Polycarbonate

## Resources

### Brochures

[Installing and testing an AFGF receptacle](#)

[AF/GF dual-purpose receptacles sell sheet](#)

### Installation instructions

[Installing and testing an AF/GF receptacle](#)

### Multimedia

[Ground Fault Circuit INterrupter \(GFCI\) demonstration](#)

### Specifications and datasheets

[Eaton Specification Sheet - TRAFGF15BK](#)

[AF/GF duplex receptacle spec sheet](#)

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)