

# Eaton TRBR15BKBXSP

Catalog Number: TRBR15BKBXSP

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 15A, Commercial, Flush, 125V, Back and side, Black, Brass, Impact-resistant nylon face, PVC body, 5-15R, Duplex, Screw, PVC, ED Box



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton commercial specification grade duplex receptacle	TRBR15BKBXSP
	<b>UPC</b>
	032664750113
<b>Product Length/Depth</b>	<b>Product Height</b>
1.24 in	4 in
<b>Product Width</b>	<b>Product Weight</b>
0.79 in	0.212 lb
<b>Certifications</b>	
cULus Listed	
NOM	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

15A

### Voltage rating

125V

### Contact material

Brass

### Features

Tamper resistant

Auto-grounding

### Application

Commercial

### Device grade

Commercial

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

PVC

### Packaging type

ED Box

### Color

Black

### Connection type

Screw

## Resources

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TRBR15BKBOXSP](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant nylon face

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)