

Eaton TRBR20W-BXSP

Catalog Number: TRBR20W-BXSP

Eaton commercial specification grade duplex receptacle, #14-10 AWG, 20A, Commercial, Flush, 125V, Back and side, White, Brass, Impact-resistant nylon face, PVC body, 5-20R, Duplex, Screw, PVC, ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade duplex receptacle	TRBR20W-BXSP
	UPC
	032664668753
Product Length/Depth	Product Height
1.24 in	4 in
Product Width	Product Weight
0.79 in	0.21 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Auto-grounding

Application

Commercial

Device grade

Commercial

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

PVC

Packaging type

ED Box

Color

White

Connection type

Screw

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TRBR20W-BXSP](#)

[Commercial grade straight blade duplex receptacles spec sheet](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

PVC body

Impact-resistant nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)