

Eaton TRIG8262W

Catalog Number: TRIG8262W

Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle, #14-10 AWG, 15A, Healthcare, Flush, 125V, Back and side, White, Brass, Impact-resistant nylon face, Glass-filled nylon base, 5-15R, Duplex, Screw, Glass-filled nylon, Core pack



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty hospital grade decorator duplex receptacle	TRIG8262W
	UPC
	032664746253
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.92 in	1 lb
Compliances	Certifications
RoHS Compliant	cULus Listed
	NOM

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Terminal guards

Tamper resistant

Application

Healthcare

Device grade

Extra heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Material

Glass-filled nylon

Packaging type

Core pack

Color

White

Connection type

Resources

Brochures

[Spec grade receptacles brochure](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TRIG8262W](#)

[TR surge protection receptacles w/audible alarm and LED indicators spec sheet](#)

Technical data sheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles](#)

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Design type

Straight blade

Face/body material

Glass-filled nylon base

Impact-resistant nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)