

Eaton TRIG8300RN

Catalog Number: TRIG8300RN

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, Orange, Brass, Impact-resistant nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Glass-filled nylon, Core pack



General specifications

Product Name	Catalog Number
Eaton Arrow Hart heavy-duty hospital grade duplex receptacle	TRIG8300RN
	UPC
	032664746284
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
0.89 in	0.189 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Brass

Features

Isolated ground

Tamper resistant

Application

Healthcare

Device grade

Heavy-duty hospital grade

Wiring method

Back and side

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Glass-filled nylon

Packaging type

Core pack

Color

Orange

Connection type

Screw

Resources

Brochures

[Arrow Hart TR extra-heavy duty receptacle sell sheet](#)

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TRIG8300RN](#)

Technical data sheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant nylon face

Glass-filled nylon base

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia