

# Eaton TRIG8300W

Catalog Number: TRIG8300W

Eaton Arrow Hart heavy-duty hospital grade duplex receptacle, #14-10 AWG, 20A, Healthcare, Flush, 125V, Back and side, White, Brass, Impact-resistant nylon face, Glass-filled nylon base, 5-20R, Duplex, Screw, Glass-filled nylon, Core pack



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Arrow Hart heavy-duty hospital grade duplex receptacle	TRIG8300W
	<b>UPC</b>
	032664746307
<b>Product Length/Depth</b>	<b>Product Height</b>
1.3 in	4.19 in
<b>Product Width</b>	<b>Product Weight</b>
0.89 in	0.189 lb
<b>Certifications</b>	
cULus Listed	
NOM	

## defaultTaxonomyAttributeLabel

### Device type

Receptacle

### Type

Duplex receptacle

### Amperage Rating

20A

### Voltage rating

125V

### Contact material

Brass

### Features

Isolated ground

Tamper resistant

### Application

Healthcare

### Device grade

Heavy-duty hospital grade

### Wiring method

Back and side

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Two-pole

### Style type

Standard

### Material

Glass-filled nylon

### Packaging type

Core pack

### Color

White

### Connection type

Screw

## Resources

### Brochures

[Arrow Hart TR extra-heavy duty receptacle sell sheet](#)

### Multimedia

[Residential straight blade receptacles](#)

### Specifications and datasheets

[Eaton Specification Sheet - TRIG8300W](#)

### Technical data sheets

[Arrow Hart extra heavy-duty hospital grade isolated ground straight blade decorator receptacles](#)

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant nylon face

Glass-filled nylon base

Receptacle type

Duplex



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)