

Eaton TRUSBAC15W-BOX

Catalog Number: TRUSBAC15W-BOX

Eaton Combination: USB Type A and C Charger, 15A 5-15R Receptacle, White, USB, Brass, Flush, Two-pole, Three-wire, Tamper resistant, Decorator



Photo is representative

General specifications

Product Name	Catalog Number
Eaton combination USB charger with duplex receptacle	TRUSBAC15W-BOX
	UPC
	032664755828
Product Length/Depth	Product Height
1.67 in	4.19 in
Product Width	Product Weight
1.3 in	0.285 lb
Certifications	
NOM	
cULus Listed	

defaultTaxonomyAttributeLabel

Type

Type AC

Amperage Rating

15A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

5A Charging

Wiring method

Screw terminals

Number of wires

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Packaging type

Retail Box

Color

White

Material

Thermoplastic

Style

Decorator

Allowable wire size

#12-14 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Combination type

USB

Resources

Multimedia

[Eaton USB Charging Receptacles](#)

[Eaton's USB charging receptacles - Never miss a moment](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

[Introduction to USB-C Duplex Receptacles](#)

Specifications and datasheets

[USB-AC charger TR receptacle spec sheet](#)

[Eaton Specification Sheet - TRUSBAC15W-BOX](#)

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia