

Eaton TRUSBC20V-BOX

Catalog Number: TRUSBC20V-BOX

Eaton Combination USB Type-C Charger, 20A 5-20R Receptacle, 5A, 125 Vac, Ivory, Box

General specifications



Photo is representative

| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton combination USB charger with duplex receptacle | TRUSBC20V-BOX |
| | UPC |
| | 032664753411 |
| Product Length/Depth | Product Height |
| 1.67 in | 4.19 in |
| Product Width | Product Weight |
| 1.3 in | 0.285 lb |
| Certifications | |
| cULus Listed | |
| NOM | |

defaultTaxonomyAttributeLabel

Type

Type C

Amperage Rating

20A

Voltage rating

125 V

Contact material

Brass

Features

Tamper resistant

5A Charging

Wiring method

Screw terminals

Number of wires

3

Three-wire

Mounting method

Flush

Number Of Poles

Two-pole

Packaging type

Retail Box

Color

Brown

Almond

Ivory

Material

Thermoplastic

Style

Decorator

Allowable wire size

#12-14 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Resources

Brochures

[USB charging devices brochure](#)

Multimedia

[Eaton USB Charging Receptacles](#)

[Fast and convenient charging made easy with Eaton's USB receptacles](#)

[Eaton's USB charging receptacles - Never miss a moment](#)

[Introduction to USB-C Duplex Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TRUSBC20V-BOX](#)

[Combination USB-C charger with TR duplex receptacle spec sheet](#)

Combination type

USB

Design type

Receptacle

Receptacle type

Two-pole, three-wire, grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia