

Eaton TWR270GY

Catalog Number: TWR270GY

Eaton residential grade duplex receptacle, #14-10 AWG, 15A, Commercial|Residential, Flush, 125V, Side and push, Gray, Brass, Weather resistant, Impact-resistant thermoplastic, 5-15R, Duplex, Screw, Thermoplastic, Core pack



Photo is representative

General specifications

Product Name	Catalog Number
Eaton residential grade duplex receptacle	TWR270GY
	UPC
	032664745201
Product Length/Depth	Product Height
1.31 in	4.19 in
Product Width	Product Weight
0.69 in	0.147 lb
Certifications	
cULus Listed NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

15A

Voltage rating

125V

Contact material

Brass

Features

Tamper resistant

Weather resistant

Application

Commercial/residential

Device grade

Standard grade

Wiring method

Side and push

Environmental conditions

Damp/wet

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Thermoplastic

Packaging type

Core pack

Environmental resistance

Weather resistant

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - TWR270GY](#)

[Arrow Hart weather resistant and tamper and weather resistant receptacles spec sheet](#)

Color

Gray

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-15R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Impact-resistant thermoplastic

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia