

Eaton TWRBR20WBXSP

Catalog Number: TWRBR20WBXSP

Eaton commercial specification grade duplex receptacle,#14-10 AWG,20A,Commercial,Flush,125V,Back and side,Ivory,Nickel-plated brass,Weather resistant,Impact-resistant nylon face,Glass-filled nylon base,5-20R,Duplex,Screw,Nylon,ED Box



Photo is representative

General specifications

Product Name	Catalog Number
Eaton commercial specification grade duplex receptacle	TWRBR20WBXSP
	UPC
	032664750298
Product Length/Depth	Product Height
1.3 in	4.19 in
Product Width	Product Weight
1.09 in	0.154 lb
Certifications	
cULus Listed	
NOM	

defaultTaxonomyAttributeLabel

Device type

Receptacle

Type

Duplex receptacle

Amperage Rating

20A

Voltage rating

125V

Contact material

Nickel plated brass

Features

Tamper resistant

Weather resistant

Auto-grounding

Application

Commercial

Device grade

Commercial

Wiring method

Back and side

Environmental conditions

Damp/wet

Number of wires

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Standard

Material

Nylon

Packaging type

ED Box

Environmental resistance

Resources

Multimedia

[Residential straight blade receptacles](#)

Specifications and datasheets

[Arrow Hart weather resistant and tamper and weather resistant receptacles spec sheet](#)

[Eaton Specification Sheet - TWRBR20WBXSP](#)

Weather resistant

Color

Ivory

Connection type

Screw

Allowable wire size

#14-10 AWG

NEMA configuration

5-20R

Torque rating

14 lbf-inch

Design type

Straight blade

Face/body material

Glass-filled nylon base

Impact-resistant nylon face

Receptacle type

Duplex



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)