

# Eaton U2R2332TDQCH

Catalog Number: U2R2332TDQCH

Eaton meter socket, Multi position resi service, 200A, Over/under, 5 x 5 inch hub open, #6-350 kcmil, 4-jaw, 1-ph, #8-250 kcmil, Horn bypass, 3-wire, Ringless, 600 Vac

## General specifications



### Product Name

Eaton meter socket

### Catalog Number

U2R2332TDQCH

### UPC

782116142927

### Product Length/Depth

5.38 in

### Product Height

14.13 in

### Product Width

24.31 in

### Product Weight

28 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

## defaultTaxonomyAttributeLabel

### Type

Multiple position residential service

### Amperage Rating

200A

### Feed type

Top/bottom

### Number of jaws

Four-jaw

### Phase

Single-phase

### Line

#6-350 kcmil

### Load

#8-250 kcmil

### Number of wires

Three-wire

### Hub type

5 x 5 hub opening

### Security

Ringless

### Voltage rating

600 V

### Bypass

Horn

### Number of sockets

2

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - SKT/2 GANG 200A 1P HO

### Specifications and datasheets

Eaton Specification Sheet - U2R2332TDQCH

Metering Equipment - Utilities Servicing Pennsylvania



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)