

# Eaton UBHTTZRS101BCH

Catalog Number: UBHTTZRS101BCH

Eaton meter socket, 1-pos resi service, 125A, Over, Small hub open, #2/0 AWG conns, 1-ph, #2/0 AWG conns, 5/16 in hex head conn screw in place of slotted, Horn bypass, Two grounding conns (#14-#2 Cu), Quadplex, 600 Vac

## General specifications



Photo is representative

### Product Name

Eaton meter socket

### UPC

786685971179

### Product Height

4.5 in

### Product Weight

10 lb

### Certifications

UL Listed

### Catalog Number

UBHTTZRS101BCH

### Product Length/Depth

12 in

### Product Width

8.65 in

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Special features

HBP, barrel lock, small hub opening

Type

Single-position residential service

Amperage Rating

125A

Feed type

Overhead

Phase

Single-phase

Ground

Quadplex ground

Utility approvals

PA : PECO Energy

Voltage rating

600 V

Specifications and datasheets

[Eaton Specification Sheet - UBHTTZRS101BCH](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)