

Eaton UG4R2352UKCCH

Catalog Number: UG4R2352UKCCH

Eaton meter socket, Multi position resi service, 200A, Over/under, Large hub cover plate hub mounted, #1/0-500 kcmil, 5-jaw, 1-ph, #8-250 kcmil, 3-wire, Ringless, Gnded 5th terminal (9 o'clock position), 600 Vac

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

786685125435

Product Height

14.13 in

Product Weight

48 lb

Certifications

UL Listed

Catalog Number

UG4R2352UKCCH

Product Length/Depth

5.38 in

Product Width

40.63 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

KCP&L approved. Center feed.

defaultTaxonomyAttributeLabel

Type

Multiple position residential service

Amperage Rating

200A

Feed type

Top/bottom

Number of jaws

Five-jaw

Phase

Single-phase

Terminals

Grounded fifth terminal (9 o'clock position)

Line

#1/0-500 kcmil

Load

#8-250 kcmil

Number of wires

Three-wire

Hub type

Large hub cover plate

Security

Ringless

Voltage rating

600 V

Number of sockets

4

Resources

Drawings

[Dimensional Drawing - SKT/4 GANG 200A 1P HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - UG4R2352UKCCH](#)

[Metering Equipment - Utilities Servicing Illinois, Iowa, Kansas, Missouri, Oklahoma and Wisconsin](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)