

Eaton UHT6R1131BCH

Catalog Number: UHT6R1131BCH

Eaton meter socket, Multi position resi service, 100A, Over/under, Small hub open, #6-350 kcmil, 4-jaw, 1-ph, #8-2/0 AWG, Horn bypass, Gnd conn (#14-#2 Cu), Triplex, 3-wire, Ringless, 600 Vac

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

782116007844

Product Height

14.13 in

Product Weight

40 lb

Certifications

UL Listed

Catalog Number

UHT6R1131BCH

Product Length/Depth

4.5 in

Product Width

56.94 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

defaultTaxonomyAttributeLabel

Type

Multiple position residential service

Amperage Rating

100A

Feed type

Top/bottom

Number of jaws

Four-jaw

Phase

Single-phase

Utility approvals

IA : Alliant (IP&L and WP&L)

WI : Alliant (IP&L and WP&L)

WI : WE Energies / Wisconsin Public Service (WPS)

Line

#6-250 kcmil

Load

#8-2/0 AWG

Number of wires

Three-wire

Hub type

Small hub opening

Security

Ringless

Voltage rating

600 V

Bypass

Horn

Number of sockets

6

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER SOCKET, 6 GANG, 100A, 1PHASE, HUB OPENING

Specifications and datasheets

Metering Equipment - Utilities Servicing Upstate New York

Eaton Specification Sheet - UHT6R1131BCH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)