

Eaton USTS132C101CH

Catalog Number: USTS132C101CH

Eaton meter socket, Instrument rated socket, 20A, Over/under, 3-5/16 inch hub cover plate, 13-jaw, Factory wired test switch, 600 Vac, Iowa approved

General specifications



Photo is representative

Product Name

Eaton meter socket

UPC

786685266817

Product Height

20 in

Product Weight

15 lb

Certifications

UL Listed

Catalog Number

USTS132C101CH

Product Length/Depth

4.38 in

Product Width

12 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Catalog Notes

Iowa approved

Type

Instrument rated socket

Amperage Rating

20A

Feed type

Top/bottom

Number of jaws

13-jaw

Hub type

3-5/16 in hub cover plate

Voltage rating

600 V

Accessories

Factory wired test switch

Number of sockets

1

Drawings

[Dimensional Drawing - SKT/SW 20A 13T FW HCP](#)

Specifications and datasheets

[Eaton Specification Sheet - USTS132C101CH](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)