

Eaton V29M28B7516CU

Catalog Number: V29M28B7516CU

Eaton General purpose ventilated transformer 75 kVA DOE 2016
Ventd XFMR 3PH 208-208Y/120, 80 °C rise, Copper,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29M28B7516CU
	UPC
	786680230110
Product Length/Depth	Product Height
24 in	43 in
Product Width	Product Weight
30.5 in	710 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
43 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

FR942

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

280E

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

75 kVA

Primary voltage

208 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

80 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

942

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29M28B7516CU](#)