

Eaton V29M28F3016ES

Catalog Number: V29M28F3016ES

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, FR940, 60 Hz, 30 kVA, upright only , Three-phase, 208 Delta V, 208Y/120 Vac, NEMA ST-20, 115°C, 30 kVA, 208 Vac-208Y/120 Vac, WS58, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29M28F3016ES
	UPC
	786680200106
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	1.1 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR940

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated type DT-3 transformer

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

208 V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Voltage rating

208-208Y/120V

Miscellaneous

Modification 1

Electrostatic shield

Weathershield

WS58

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29M28F3016ES](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)