

# Eaton V29M37T1516

Catalog Number: V29M37T1516

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, FR939, 60 Hz, 15 kVA, Three-phase, 208 Delta V, 380Y/220 Vac, NEMA ST-20, 15 kVA, 208 Vac-380Y/220 Vac, WS57, E0342B, DOE 2016



Photo is representative

## General specifications

|  |                                  |
|--|----------------------------------|
| <b>Product Name</b>  | <b>Catalog Number</b>            |
| Eaton General purpose ventilated transformer   | V29M37T1516                      |
|  | <b>UPC</b>                       |
|  | 786680220883                     |
| <b>Product Length/Depth</b>  | <b>Product Height</b>            |
| 17.75 in   | 28 in                            |
| <b>Product Width</b>   | <b>Product Weight</b>            |
| 21.88 in   | 232 lb                           |
| <b>Warranty</b>  | <b>Compliances</b>               |
| Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | <b>Certifications</b>            |
|  | UL Listed                        |
|  | <b>Catalog Notes</b>             |
|  | 10 CFR Part 431 (2016) Efficient |

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Frame

FR939

### Insulation

220 °C

### Mounting

Floor or wall, upright only

### Tap size

2 at +2.5%, 4 at -2.5%

### Type

Energy-efficient ventilated type DT-3 transformer

### Wiring connection

E0342B

## Miscellaneous

### Weathershield

WS57

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

208 V

### Secondary Voltage

380Y/220 V

### Sound Level

NEMA ST-20

### Temperature rise

150 °C rise

### Volt ampere rating

15 kVA

### Voltage rating

208 Vac-380Y/220 Vac

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - V29M37T1516](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)