

Eaton V29M44T3016

Catalog Number: V29M44T3016

Eaton General Purpose Ventilated Transformer, AL windings, DOE 2016, 3PH , PV 208 DELTA, SV 440 DELTA, 30 kVA, 150C rise, 220C, NEMA 2 FR940, E0299D



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29M44T3016
	UPC
	786680241727
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	404 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
10 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

940

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated dry-type transformer

Wiring connection

E0299D

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

208 V

Secondary Voltage

440 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

30 kVA

Miscellaneous

Weathershield

WS58

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29M44T3016](#)