

# Eaton V29M47B15CUNVLS50

Catalog Number: V29M47B15CUNVLS50

General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 208V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 480Y/277V, 80°C, 15 kVA, Cu windings



Photo is representative

## General specifications

### Product Name

Eaton General purpose ventilated transformer

### Catalog Number

V29M47B15CUNVLS50

### UPC

786680028984

### Product Length/Depth

0.001 in

### Product Height

0.001 in

### Product Width

0.001 in

### Product Weight

0.001 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed

### Catalog Notes

Totally enclosed non-ventilated, Low sound equal to 50 dB

## Physical Attributes

### Coil material

Copper

### Design

DT-3

### Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### Primary voltage

208 V

### Secondary Voltage

480Y/277 V

### Temperature rise

80 °C rise

## Miscellaneous

### Modification 1

Low sound 50 dB

## Resources

### Brochures

[NEMA Premium Efficient Transformers Product Aid](#)

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[NEMA Premium Efficient Transformers Data Sheet](#)

[Eaton Specification Sheet - V29M47B15CUNVLS50](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)