

Eaton V29M47B45CUNVLS50

Catalog Number: V29M47B45CUNVLS50

General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 208V, Taps: 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 480Y/277V, 80°C, 45 kVA, Cu windings



Photo is representative

General specifications

Product Name

Eaton General purpose ventilated transformer

Catalog Number

V29M47B45CUNVLS50

UPC

786680029004

Product Length/Depth

0.001 in

Product Height

0.001 in

Product Width

0.001 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Totally enclosed non-ventilated, Low sound equal to 50 dB

Physical Attributes

Coil material

Copper

Design

DT-3

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

45 kVA

Primary voltage

208 V

Secondary Voltage

480Y/277 V

Temperature rise

80 °C rise

Miscellaneous

Modification 1

Low sound 50 dB

Resources

Brochures

[NEMA Premium Efficient Transformers Product Aid](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V29M47B45CUNVLS50](#)

[NEMA Premium Efficient Transformers Data Sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)