

Eaton V29M48T7516

Catalog Number: V29M48T7516

75 kVA DOE 2016 Ventd XFMR 3PH 208-480 DELTA, 150 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29M48T7516
	UPC
	786680230943
Product Length/Depth	Product Height
24 in	43 in
Product Width	Product Weight
30.5 in	630 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
32 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR942

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

E0299D

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

75 kVA

Primary voltage

208 V

Secondary Voltage

480 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

75 kVA

Miscellaneous

Weathershield

942

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29M48T7516](#)