

Eaton V29R22T1216

Catalog Number: V29R22T1216

Eaton General purpose ventilated transformer, NEMA 2, FR943, 60 Hz, 112.5 kVA, Three-phase, 208 Delta V, 240 Delta/120 Midtap Vac, NEMA ST-20, 1 at +5%, 2 at -5%, 112.5 kVA, 208 Vac-240 Vac/120 Vac, WS60, E0432A, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29R22T1216
	UPC
	786680220678
Product Length/Depth	Product Height
31.5 in	51 in
Product Width	Product Weight
34.5 in	975 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR943

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

1 at +5%, 2 at -5%

Type

Energy-efficient ventilated type DT-3 transformer

Wiring connection

E0432A

Miscellaneous

Weathershield

WS60

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

112.50 kVA

Primary voltage

208 V

Secondary Voltage

240 V, 120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

112.5 kVA

Voltage rating

208 Vac-240 Vac/120 Vac

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29R22T1216](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)