

# Eaton V29R47B12CUNVLS50

Catalog Number: V29R47B12CUNVLS50

Eaton General-Purpose Transformer, Dry Type Distribution, DT-3, Three-phase, PV: 208V, Taps: 1 at +5% FCAN, 2 at -5% FCBN, SV: 480Y/277V, 80°C, 50 kVA, Cu windings, Frame: 918AN



Photo is representative

## General specifications

### Product Name

Eaton General purpose ventilated transformer

### Catalog Number

V29R47B12CUNVLS50

### UPC

786680029028

### Product Length/Depth

30.68 in

### Product Height

62.18 in

### Product Width

31.44 in

### Product Weight

1922 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

### Catalog Notes

Totally enclosed non-ventilated, Low sound equal to 50 dB

## Physical Attributes

### Coil material

Copper

### Design

DT-3

### Frame

918AN

### Tap size

1 at +5% FCAN, 2 at -5% FCBN

### Type

Dry Type Distribution Transformer

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

50 kVA

### Primary voltage

208 V

### Secondary Voltage

480Y/277 V

### Temperature rise

80 °C rise

## Miscellaneous

### Modification 1

Low sound 50 dB

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - V29R47B12CUNVLS50](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)