

Eaton V29R47T2216

Catalog Number: V29R47T2216

Eaton General purpose ventilated transformer, NEMA 2, FR944, 60 Hz, 225 kVA, Floor, Three-phase, 208 Delta V, 480Y/277 Vac, NEMA ST-20, 1 at +5%, 2 at -5%, 225 kVA, 208 Vac-480Y/277 Vac, WS61, E0351A, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V29R47T2216
	UPC
	786680175510

Product Length/Depth	Product Height
33.5 in	60 in

Product Width	Product Weight
38 in	1.1 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

[Catalog Notes](#)

10 CFR Part 431 (2016) Efficient



Powering Business Worldwide

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR944

Insulation

220 °C

Material

Aluminum

Mounting

Floor

Tap size

1 at +5%, 2 at -5%

Type

Energy-efficient ventilated type DT-3 transformer

Wiring connection

E0351A

Miscellaneous

Weathershield

WS61

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

225 kVA

Primary voltage

208 V

Secondary Voltage

480Y/277 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

225 kVA

Voltage rating

208-480Y/277V

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V29R47T2216](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)