

Eaton V39M22T1516

Catalog Number: V39M22T1516

15 kVA DOE 2016 Ventd XFMR 3PH 400-240 DELTA 120V
LIGHTING TAP (PH B), 150 °C rise, Aluminum,



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V39M22T1516
	UPC
	786680230707
Product Length/Depth	Product Height
17.75 in	28 in
Product Width	Product Weight
21.88 in	224 lb
Compliances	Certifications
DOE2016 Efficient	UL Listed
Catalog Notes	
83 CFR Part 431 (2016) Efficient	

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Frame

FR939

Insulation

220 °C

Mounting

Floor or wall

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated transformer

Wiring connection

282L

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

15 kVA

Primary voltage

400 V

Secondary Voltage

240 V, 120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

15 kVA

Miscellaneous

Weathershield

939

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V39M22T1516](#)