

Eaton V43M51T88X

Catalog Number: V43M51T88X

Eaton General purpose ventilated transformer, dry type distribution transformer, DT-3, aluminum, NEMA 2, 916A, 50-60 Hz, three-phase, 416 V, 416Y/240 V, 2 at +2.5% FCAN, 4 at -2.5% FCBN, 150 °C rise, 80 KVA, indoor-outdoor, 280P



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V43M51T88X
	UPC
	786680081903
Product Length/Depth	Product Height
23.42 in	48.56 in
Product Width	Product Weight
28.22 in	789 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

DT-3

Enclosure

NEMA 2

Frame

916A

Tap size

2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Dry Type Distribution Transformer

Wiring connection

280P

Performance Ratings

Frequency rating

50-60 Hz

Primary voltage

416 V

Secondary Voltage

416Y/240 V

Temperature rise

150 °C rise

Volt ampere rating

80 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - V43M51T88X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)