

Eaton V47M28T3016

Catalog Number: V47M28T3016

Eaton General purpose ventilated transformer, Aluminum windings, NEMA 2, 60 Hz, 30 kVA, Floor or wall, upright only , Three-phase, 480Y, 208Y/120 Vac, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 30 kVA, 480Y-208Y/120 Vac, DOE 2016



Photo is representative

General specifications

| | |
|---|----------------------------------|
| Product Name | Catalog Number |
| Eaton General purpose ventilated transformer | V47M28T3016 |
| | UPC |
| | 786680196874 |
| Product Length/Depth | Product Height |
| 21.13 in | 36.88 in |
| Product Width | Product Weight |
| 24.88 in | 1.1 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | Catalog Notes |
| | 10 CFR Part 431 (2016) Efficient |

Physical Attributes

Coil material

Aluminum

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

2 at +2.5%, 4 at -2.5%

Type

Energy-efficient ventilated type DT-3 transformer

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

480Y V

Secondary Voltage

208Y/120 V

Sound Level

NEMA ST-20

Temperature rise

150 °C rise

Volt ampere rating

30 kVA

Voltage rating

480Y-208Y/120 Vac

Resources

Brochures

[Eaton's high-efficiency dry-type transformers](#)

[Eaton's low-voltage dry-type distribution transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V47M28T3016](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)