

# Eaton V48D28F1216CUESLS47

Catalog Number: V48D28F1216CUESLS47

Eaton General purpose ventilated transformer, NEMA 2, 60 Hz, 220°C, 112.5 kVA, upright only , Three-phase, 480 Delta V, 208Y/120 Vac, Low sound 47 dB, +2 at 2.5%, -2 at 2.5%, 115°C, 112.5 kVA, 480 Vac-208Y/120 Vac, DOE 2016



Photo is representative

## General specifications

|  |                                  |
|--|----------------------------------|
| <b>Product Name</b>  | <b>Catalog Number</b>            |
| Eaton General purpose ventilated transformer   | V48D28F1216CUESLS47              |
|  | <b>UPC</b>                       |
|  | 786680204111                     |
| <b>Product Length/Depth</b>  | <b>Product Height</b>            |
| 31.5 in  | 51 in                            |
| <b>Product Width</b>   | <b>Product Weight</b>            |
| 34.5 in  | 1.1 lb                           |
| <b>Warranty</b>  | <b>Compliances</b>               |
| Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | <b>Certifications</b>            |
|  | UL Listed                        |
|  | <b>Catalog Notes</b>             |
|  | 10 CFR Part 431 (2016) Efficient |

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 2

### Insulation

220 °C

### Mounting

Floor or wall, upright only

### Tap size

+2 at 2.5%, -2 at 2.5%

### Type

Energy-efficient ventilated type DT-3 transformer

## Performance Ratings

### Efficiency

10 CFR Part 431-2016 (DOE 2016)

### Frequency rating

60 Hz

### Kva Rating

112.50 kVA

### Primary voltage

480 V

### Secondary Voltage

208Y/120 V

### Sound Level

47 dB

### Temperature rise

115 °C rise

### Volt ampere rating

112.5 kVA

### Voltage rating

480 Vac-208Y/120 Vac

## Miscellaneous

### Modification 1

Electrostatic shield

## Resources

### Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

### Specifications and datasheets

[Eaton Specification Sheet - V48D28F1216CUESLS47](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)