

Eaton V48D28F3016CUESLS42

Catalog Number: V48D28F3016CUESLS42

Eaton General purpose ventilated transformer, Copper windings, NEMA 2, 60 Hz, 220°C, 30 kVA, upright only , Three-phase, 480 Delta V, 208Y/120 Vac, Low sound 42 dB, +2 at 2.5%, -2 at 2.5%, 115°C, 30 kVA, 480 Vac-208Y/120 Vac, DOE 2016



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	V48D28F3016CUESLS42
	UPC
	786680204654
Product Length/Depth	Product Height
21.13 in	36.88 in
Product Width	Product Weight
24.88 in	1.1 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year DOE2016 Efficient from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	UL Listed
	Catalog Notes
	10 CFR Part 431 (2016) Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Insulation

220 °C

Mounting

Floor or wall, upright only

Tap size

+2 at 2.5%, -2 at 2.5%

Type

Energy-efficient ventilated type DT-3 transformer

Performance Ratings

Efficiency

10 CFR Part 431-2016 (DOE 2016)

Frequency rating

60 Hz

Kva Rating

30 kVA

Primary voltage

480 V

Secondary Voltage

208Y/120 V

Sound Level

42 dB

Temperature rise

115 °C rise

Volt ampere rating

30 kVA

Voltage rating

480 Vac-208Y/120 Vac

Miscellaneous

Modification 1

Electrostatic shield

Resources

Brochures

[Eaton's low-voltage dry-type distribution transformers](#)

[Eaton's high-efficiency dry-type transformers](#)

Specifications and datasheets

[Eaton Specification Sheet - V48D28F3016CUESLS42](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)